UNIT	CONDENSER	
MODEL #	eco-ATC-1769A	SCALE NTS


EVAPCO, INC. Evapeo

DWG. # REV. WB3241812-DRC-ST DATE<sub>11/27/2025</sub> SERIAL #


**FACE D** 


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





**FACE A** 





**SHIPPING** 77100 lbs+ [34975] kg+ WEIGHT

OPERATING WEIGHT

98700 lbs+ [44770] kg+

HEAVIEST SECTION WEIGHT

34630 lbs+ [15710] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR