

UNIT		CONDENSER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	WB3243606-DRC-ST	REV.	-
MODEL #		eco-ATC-2557A	SCALE		NTS	SERIAL #		DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

1'-10 1/4" [565] *

(8) 4" [100] PE

(8) 4" [100] PE

REFRIG IN

REFRIG OU

2'-1 1/4" [643]

1'-5" [433]

3 5/8" [92]

(4) 3" [80] MPT OVERFLOW

5 1/8" [130]

24'-1 1/8" [7344]

5'-9 1/4" [1759] *

(8) 4" [100] PE

(8) 4" [100] PE

REFRIG IN

REFRIG OU

11'-4 3/4" [3473]

11'-5 3/4" [3499]

11'-10" [3607]

3'-3/8" [924] *

8'-3 5/8" [2532]

16'-5 7/8" [5026]

6" [154] *

8'-2 1/4" [2494]

4'-8" [1422]

7" [178]

1'-3 1/4" [387]

1'-11 1/8" [587]

36'-2 1/2" [11036]

1'-11 1/8" [587]

SHIPPING WEIGHT

97440 lbs+ [44200] kg+

OPERATING WEIGHT

137480 lbs+ [62360] kg+

HEAVIEST SECTION WEIGHT

20410 lbs+ [9260] kg+

NO. OF SHIPPING SECTIONS

6

DRAWN BY:

SLR