NIT CONDENSER	DWG. # WB3TM2412-DRC-ST	REV.
ODEL # eco-ATC-1002A SCALE NTS	EVAPCO, INC. EVEPCO SERIAL #	DATE 12/15/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	FACE B PLAN VIEW FACE A FACE A	FACE D
(2) 2" [50] MPT REFRIG OUT ON MAKE-UP 2'-1 1/4" [643] (2) 2" [50] MPT REFRIG OUT ON MAKE-UP (2) 3" [80] MPT DRAIN (2) 3" [80] MPT DRAIN (3) 5 1/4" (4) 4" [108] (5) 1/4" (108] (1) 29 3 3 4" (2) 2" [80] MPT DRAIN (3) 5 1/4" (4) 4" [108] (5) 1-11 3/4" (1) 1822]	2'-6 3/8" * [1772] * 10'-5 1/8" [387] 10'-5 1/8" [3180] 16'-7 3/8" [15064] 6'-2 1/4" [1884] 1-3" [433] -2) 3" [80] MPT OVERFLOW 11'-11 3/4" [3651] 24'-2" [432] 11'-11 3/4" [3651] 24'-2" [432] 11'-11 3/4" [366]	1'-5" _ [432]
FACE B SHIPPING WEIGHT 45120 lbs+ [20470] kg+	OPERATING 57760 lbs+ [26200] kg+ HEAVIEST SECTION 20010 lbs+ [9080] kg+ NO. OF SHIPPING SECTIONS 4 DRAW	WN BY: