| UNIT | CONDENSER | |
|---------|-------------|-----------|
| MODEL # | eco-ATC-89A | SCALE NTS |

EVAPCO, INC. Evapeo



DWG. # REV. WB3040610-DRE-ST DATE_{11/26/2025} SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

METRIC [mm]

8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN**


FACE C


FACE B PLAN VIEW



FACE D

FACE A





SHIPPING 4290 lbs+ [1950] kg+ WEIGHT

OPERATING WEIGHT

5460 lbs+ [2480] kg+

HEAVIEST SECTION WEIGHT

3780 lbs+ [1715] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: