UNIT CLOSED CIDCUIT COOLED		DWG.# REV
CLOSED CIRCUIT COOLER MODEL # ESW4 14-23M22-LP SCALE NTS	EVAPCO, INC. Evapeo	WX414222406-DRA-ST
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING	FACE B PLAN VIEW	
2" [50] MPT		9'-5 5/8" [2886] 9'-5 5/8" [2962] 9'-8 5/8" [2962]
SHIPPING WEIGHT 34390 lbs+ [15600] kg+ OPERATING WEIGHT	52250 lbs+ [23705] kg+ HEAVIEST SECTION WEIGHT 23240 lbs+ [10545] kg+	NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG