CLOSED CIRCUIT COOLER MODEL# ESW4 12-25K18-SF

EVAPCO, INC. EVAPCO



WX412182410F-DRA-ST

10/16/2025


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 8. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE C


SERIAL#



FACE A



NTS



SHIPPING 31560 lbs+ [14320] kg+ WEIGHT

OPERATING WEIGHT

46920 lbs+ [21285] kg+

HEAVIEST SECTION WEIGHT

24900 lbs+ [11295] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT