CLOSED CIRCUIT COOLER MODEL# ESW4 12-35J18-SF NTS

EVAPCO, INC. EVAPCO



WX412183610F-DRA-ST SERIAL#

11/9/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HÉAVIEST SECTION IS COIL SECTION

3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE


4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING


6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]


7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]

8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING **FACE C**



FACE A





SHIPPING 32290 lbs+ [14650] kg+ WEIGHT

OPERATING WEIGHT

47650 lbs+ [21615] kg+

HEAVIEST SECTION WEIGHT

24900 lbs+ [11295] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT