


UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-43K18X-LP

EVAPCO, INC. 


DWG. # WX41218X4806P-DRA-ST

REV -
SERIAL #
DATE: 2/18/2026

NOTES:
 1. (M)- FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS COIL SECTION
 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 4. +UNIT WEIGHT DOES NOT INCLUDE
 ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. 3/4" [19MM] DIA. MOUNTING HOLES.
 REFER TO RECOMMENDED STEEL
 SUPPORT DRAWING
 6. MAKE-UP WATER PRESSURE
 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 7. DIMENSIONS LISTED AS FOLLOWS:
 ENGLISH FT-IN
 [METRIC] [mm]
 8. * - APPROXIMATE DIMENSIONS DO NOT USE
 FOR PRE-FABRICATION OF CONNECTING PIPING
 9. COIL CONNECTIONS LOCATED ON FACES B AND D




FACE B
PLAN VIEW




FACE C

FACE D

FACE A



FACE B



FACE A

SHIPPING
WEIGHT

23520 lbs+ [10670] kg+

OPERATING
WEIGHT

35250 lbs+ [15990] kg+

HEAVIEST SECTION
WEIGHT

15370 lbs+ [6975] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT