


UNIT CLOSED CIRCUIT COOLER  
MODEL # ESW4 12-44J18X-LP

EVAPCO, INC. 


DWG. # WX41218X4808P-DRA-ST

REV -

SCALE NTS  
NOTES:  
1. (M)- FAN MOTOR LOCATION  
2. HEAVIEST SECTION IS COIL SECTION  
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)  
5. 3/4" [19MM] DIA. MOUNTING HOLES.  
REFER TO RECOMMENDED STEEL  
SUPPORT DRAWING  
6. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]  
8. \* - APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING PIPING  
9. COIL CONNECTIONS LOCATED ON FACES B AND D




FACE B  
PLAN VIEW




FACE C

FACE D



FACE B & D  
COIL CONNECTIONS



FACE A

FACE B

FACE A

SHIPPING  
WEIGHT

25770 lbs+ [11690] kg+

OPERATING  
WEIGHT

38300 lbs+ [17375] kg+

HEAVIEST SECTION  
WEIGHT

17680 lbs+ [8020] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT

DATE: 2/19/2026