

UNIT		CONDENSER		EVAPCO, INC. evapco	DWG. # WB3171410-DRD-ST		REV. -																						
MODEL # eco-ATC-898A		SCALE NTS			SERIAL #		DATE 1/23/2026																						
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]					FACE C (M) (2) ACCESS DOOR FACE B PLAN VIEW FACE D FACE A																								
1'-9 3/8" [543] 2'-10 1/2" [876] 1'-11 1/8" [589] 3" [76] (4) 4" [100] PE REFRIG IN (4) 4" [100] PE REFRIG OU (2) 2" [50] MPT MAKE-UP (2) 2" [50] MPT DRAIN (2) 3" [80] MPT OVERFLOW 5 1/8" [130] 17'-4 1/8" [5286] FACE B 4'-3/4" [1238] 2'-2 3/8" [670] 8'-2 1/2" [2503] 13'-8 3/4" [4185] 6" [154] 5'-6 1/4" [1681] 2'-10 1/4" [870] 1'-3" [383] 8'-1 1/4" [2445] 8'-1 1/4" [2470] 8'-5 1/2" [2578] FACE A					SHIPPING WEIGHT 37520 lbs+ [17020] kg+					OPERATING WEIGHT 47500 lbs+ [21550] kg+					HEAVIEST SECTION WEIGHT 16680 lbs+ [7570] kg+					NO. OF SHIPPING SECTIONS 4					DRAWN BY: SLR				