UNIT CLOSED CIRCUIT COOLER	EVADCO :	TNC evapco	DWG. # WX41218X2408F-DRA-ST	REV -
MODEL# ESW4 12-24L18X-LF SCALE NTS	EVAPCO,	INC. evapeo	SERIAL#	DATE: 11/28/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWING: 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIF	(4) 4" [100] BFW - FLUID IN 0	FACE B PLAN VIEW (4) 4" [100] BFW FLUID OUT * 2'-3" [686]	CE A	ACE D
2'-4" [711] 4" [101] 4 1/4" [107] 5 1/4" [132] 11'-10" [3607] FACE B	* 4'-4 5/8"	(4)1/2" [15] FPT VENT	(M) ACCESS DOOR 8'-3 9'-10 8'-0" 2'-3 1 486] CE A	9]
SHIPPING WEIGHT 28690 lbs+ [13015] kg+ OF	42890 lbs+ [19455] kg+	HEAVIEST SECTION 21980 lbs+ [9970] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT