CLOSED CIRCUIT COOLER MODEL# ESW4 9-36H6-LP NTS


## EVAPCO, INC. Evapeo




WX409063612P-DRA-ST SERIAL# 11/1/2025

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 8. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



## **FACE C**



## **FACE A**



**FACE A** 

NO. OF SHIPPING SECTIONS DRAWN BY: OPERATING SHIPPING 9090 lbs+ [4125] kg+ 12580 lbs+ [5710] kg+ HEAVIEST SECTION 6860 lbs+ [3110] kg+ AWT WEIGHT WEIGHT WEIGHT