CLOSED CIRCUIT COOLER			EVAPCO,	TNC	evapco	DWG.# WX409184810P-DRA-S	
MODEL#	ESW4 9-45G18-SP	SCALE NTS	LVAFCO			SERIAL#	DATE: 11/28/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DE GVD DE FLG DE 4. +UNIT V ACCES 5. 3/4" [19] REFER SUPPO 6. MAKE-U 20 psi M	N MOTOR LOCATION ST SECTION IS COIL SECENOTES MALE PIPE THRE NOTES FEMALE PIPE THE ENOTES BEVELED FOR VENOTES GROOVED NOTES FLANGE WEIGHT DOES NOT INCLUSORIES (SEE ACCESSOF MMJ DIA. MOUNTING HOL TO RECOMMENDED STE RT DRAWING JP WATER PRESSURE MIN [137 KPa], 50 psi MAX [SIONS LISTED AS FOLLO	EAD READ VELDING  UDE RY DRAWINGS) ES. EEL	(2) 4" [100] BFW	FACE B PLAN VIEW  (2) 4" [100] BFW FLUID OUT	(M)	CE C	∏ FACE D
[ME1 8. * - APPI FOR PF	LISH FT-IN 'RIC] [mm] ROXIMATE DIMENSIONS RE-FABRICATION OF CON	INECTING PIPING		* 2'-10 1/2" [876]	FAC	CE A	
9. COIL C	ONNECTIONS LOCATED ( T	ON FACES B AND		* 2'-2 3/8" [670]	F		-1'-0 7/8" [327]
	(M)		* 2'-8" [813] FACE B & D COIL CONNECTI	_* 2'-10 3/4" [883]	F(M) ACCESS (DOOR)	C = ] (ACCESS) L(M)   DOOR	9'-3 1/4" [2826]
	2" [50] MPT — MAKE-UP 2" [50] MPT — DRAIN	0	3" [80] MPT OVERFLOW	(2)1/2" [15] FPT VENT			19'-4 7/8" [5917] 10'-1 5/8" [3090]
2	2'-3" [686]						
	3 3/8" [86] 4 1/4" [107] 5 1/4" [132]		2'-5 5/8" [752]	2'-2 1/4" [667]		-0" 86] CE A	
[2578]							
SHIPPING WEIGHT	22020 lbs+ [9990] k		31260 lbs+ [14180] kg+	HEAVIEST SECTION WEIGHT	15220 lbs+ [6905] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT