UNIT CLOSED CIRCUIT COOLER		CO TNIC	evança	DWG.# WX409124808P-DRA-ST	REV _
MODEL #	TS EVAP	co, inc.		SERIAL#	DATE: 11/28/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWII 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]		FACE B PLAN VIEW	FACE C (M)	FACE D	
8. * - APPROXIMATE DIMENSIONS DO NOT U FOR PRE-FABRICATION OF CONNECTING			FACE A	_1'-0 7/8" [327]	
(M) * 2'-8" [813]			[] [] [] [] [] [] [] [] [] []	ACCESS (DOOR) 9'-3 1/4" [2826]	
4" [100] BFW — FLUID IN	4" [100] BFW FLUID OUT			18'-1 3/	 8" [5523]
2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 2'-3" [686]	3" [80] MPT OVERFLOW * 2'-3" [686]	1/2" [15] FPT VENT		8'-10 1/8" [2696]	
3 3/8" [86]	* 2'-2 3/8" [670] -1'-6 3/8" [465]	2'-1"	11'-11 3/4"		
4 1/4"	2'-5 5/8" [752]	[635]	[3651]	- 1	
5 1/4" 8'-5 1/2					
[2578] FACE B			FACE A		
SHIPPING WEIGHT 14350 lbs+ [6510] kg+	OPERATING WEIGHT 20550 lbs+ [9325	6] kg+ HEAVIEST SECTION WEIGHT	10080 lbs+ [4575] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT