UNIT CONDENSER			EVAPCO, INC. Evapeo				OWG. # CW4C071810-DRA-ST REV	
MODEL #	eco-ATC-532A	SCALE NTS	T EVAL	<b>CO, 1</b>	NC.		SERIAL #	DATE <sub>12/14/2025</sub>
2. HÉAVIES 3. MPT DE FPT DEN BFW DE GVD DE FLG DEN 4. +UNIT W ACCESS 5. MAKE-U 20 psi M 6. *-APPRC FOR PR PIPING 7. 3/4" [19n RECOMI	I MOTOR LOCATION BT SECTION IS FAN/CASIN NOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES GROOVED NOTES GROOVED NOTES FLANGE DIES PLAIN END /EIGHT DOES NOT INCLUI SORIES (SEE ACCESSORY P WATER PRESSURE IN [137 kPa], 50 psi MAX [3-0) DIMATE DIMENSIONS DO E-FABRICATION OF CONN nm] DIA. MOUNTING HOLE MENDED STEEL SUPPOR IONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	DE DRAWINGS)  44 kPa] NOT USE ECTING  S. REFER TO DRAWING.		PLAN V	ACE B	ACCESS DOO	FACE A	ESS DOOR  FACE D
2'-1 [50] M MAKE-2" [50] M DRA I'-11 [58]	UP PT J/8" 	REFRIG OUT	2'-11 3/8" [ 899 ] 1'-10 7/8" * [ 1622 ] 13'-3 1/4" * [ 133 ] * 5'-1/4" [ 1530 ] 1'-3" [ 381 ] 3" [80] MPT OVERFLOW	/2" ] 1'-4.7 [ 42			[18'-0" [5486]	
SHIPPING	FACI		OPERATING 25020 lbc.		HEAVIEST SECTION		FACE A  NO. OF SHIPPING SECTIONS	DRAWN BY:
WEIGHT	22520 lbs+ [102	15] kg+	WEIGHT 25930 lbs+	[11765] kg+	WEIGHT	<sup>JN</sup> 19500 lbs+ [8850] kg+	NO. OF SHIPPING SECTIONS 2	TAM