CLOSED CIRCUIT COOLER


MODEL # ESW4 9-36I6-LP SCALE NTS

EVAPCO, INC. EVAPCO


DWG.# WX409063612P-DRA-ST REV SERIAL# DATE: 10/29/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]
- 8. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE C



FACE D

FACE A



FACE A

SHIPPING WEIGHT 9120 lbs+ [4140] kg+ OPERATING WEIGHT 12610 lbs+ [5720] kg+ HEAVIEST SECTION 6860 lbs+ [3110] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT