UNIT CONDENSER						DWG. # CW4C072408-DRA-ST REV		
10DEL #	eco-ATC-634A	SCALE NTS		APCO, II	NC. evapeo	SE	ERIAL #	DATE 12/15/2025
2. HEAVII 3. MPT D FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT 5. MAKE- 20 psi I 6. *-APPF FOR PI PIPING 7. 3/4" [15 RECON	AN MOTOR LOCATION EST SECTION IS FAN/CASIN ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE DENOTES GROOVED ENOTES PLAINGE NOTES PLAIN END WEIGHT DOES NOT INCLUE SSORIES (SEE ACCESSORY -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONNI G 9mm] DIA. MOUNTING HOLE: MMENDED STEEL SUPPORT ISIONS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	D EAD ELDING DE DRAWINGS) 14 kPa] NOT USE ECTING S. REFER TO	<u>P</u>	FACE B LAN VIEW	ACCESS DOOR	ACE A	ACCESS DOOR	FACE D
(2) 2" [50 [  1'-11 ]  [ 587	2'-3" (4) 4" [100] PE (686 ] (4) 4" [100] PE (7) [100] PE	REFRIG IN REFRIG OUT  1'-3 [ 381	2'-11 3/8" 1'-10 7/8"				2 1/2"	1'-5 1/8" [ 435 ]
SHIPPING WEIGHT	34500 lbs+ [1568	50] kg+	OPERATING 37230 WEIGHT	0 lbs+ [16890] kg+	HEAVIEST SECTION 13620 lbs+ [6180]	kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: TAM
			-					