UNIT COOLING TOWER		VER
MODEL #	AT 312-4054	SCALE NTS

EVAPCO, INC. Evapeo


DWG. # REV. T3125448-DRD-ST DATE 11/14/2025 SERIAL #


FACE D


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]

FACE C







DRAWN BY: KDS NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 38820 lbs+ [17610] kg+ 66630 lbs+ [30225] kg+ 8760 lbs+ [3975] kg+ WEIGHT WEIGHT WEIGHT