CLOSED CIRCUIT COOLER	EVAPCO, INC. evapco * WX409184	806P-DRA-ST REV -
MODEL# ESW4 9-43K18-SP SCALE NTS	LVAPCO, LINCI	DATE: 10/16/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]	FACE B PLAN VIEW (2) 4" [100] BFW FLUID IN * 1'-7 1/2" [495] FACE A	FACE D
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPIT 9. COIL CONNECTIONS LOCATED ON FACES B AT	* 2'-8"	1'-0 7/8" [327] (ACCESS) DOOR
		9'-3 1/4" [2826]
2" [50] MPT — MAKE-UP — 2" [50] MPT — DRAIN	(2)1/2" [15] FPT VENT OVERFLOW	8'-10 5/8" [2709]
2'-3" [686]		
3 3/8" [86] 4 1/4" [107] 5 1/4" [132] 8'-5 1/2"	2'-5 5/8" 2'-2 1/4" 18'-0" [5486] [FACE A	
[2578]		
SHIPPING WEIGHT 19180 lbs+ [8700] kg+ OPER WE	ATING ATING 27210 lbs+ [12345] kg+ HEAVIEST SECTION 11620 lbs+ [5270] kg+ NO. OF SHIPPING SEC	TIONS 2 DRAWN BY: AWT