					160	<b>L</b>	T
CLOSED CIRCUIT COOLER			EVAPCO, INC. EVEPCO SERIAL# WX409124810P-DRA-ST		REV -		
MODEL#	ESW4 9-45L12-SP	NTS	EVAPCO,	TIAC.		SERIAL#	DATE: 11/25/2025
2. HEAVIE 3. MPT DE FPT DE BFW DE GVD DE FLG DE 4. +UNIT V ACCES 5. 3/4" [19I REFER SUPPO 6. MAKE-L 20 psi M 7. DIMENS ENG	N MOTOR LOCATION ST SECTION IS COIL SECTION NOTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD NOTES BEVELED FOR WELDIN NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUDE SORIES (SEE ACCESSORY DRAM) DIA. MOUNTING HOLES. TO RECOMMENDED STEEL RT DRAWING IP WATER PRESSURE IN [137 kPa], 50 psi MAX [344 kFIONS LISTED AS FOLLOWS:	AWINGS)		FACE B PLAN VIEW	FACE		
8. * - APPF	RIC] [mm] ROXIMATE DIMENSIONS DO NO E-FABRICATION OF CONNECTI				FACE	<u>-1'-0 7/8" [327]</u>	
	[25	1/2" -578]	4" [100] BFW FLUID OUT  3" [80] MPT OVERFLOW  * 2'-10 1/2" [876]  * 2'-2 3/8" [670]  1'-6 3/8" [465]  2'-5 5/8" [752]  * 2'-10 3/4" [883]	1/2" [15] FPT VENT		9'-3 1/4" [2826]  9'-5 5/8" [2887]	7/8" [5713] 
SHIPPING			g 22620 lbc : [10265] l :	HEAL/JEST SECTION			DRAWN BY:
WEIGHT	15890 lbs+ [7210] kg+	OPERATIN WEIGHT	<sup>G</sup> 22620 lbs+ [10265] kg+	HEAVIEST SECTION WEIGHT	<sup>DN</sup> 11640 lbs+ [5280] kg-	NO. OF SHIPPING SECTIONS 2	AWT