

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-36I6-LP

EVAPCO, INC.



DWG. # WX409063612P-DRA-ST

REV -


SERIAL #

DATE: 2/10/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING


FACE C




FACE B
PLAN VIEW

FACE D

FACE A



FACE A



FACE B

SHIPPING
WEIGHT

9120 lbs+ [4140] kg+

OPERATING
WEIGHT

12610 lbs+ [5720] kg+

HEAVIEST SECTION
WEIGHT

6860 lbs+ [3110] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT