

UNIT CLOSED CIRCUIT COOLER  
MODEL # ESW4 9-45K12-LP

EVAPCO, INC.




DWG. # WX409124810P-DRA-ST

REV -  
SERIAL #  
DATE: 2/6/2026

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B

PLAN VIEW

FACE C



FACE D



FACE A

SHIPPING  
WEIGHT

15910 lbs+ [7220] kg+

OPERATING  
WEIGHT

22640 lbs+ [10270] kg+

HEAVIEST SECTION  
WEIGHT

11690 lbs+ [5300] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT