UNIT	COOLING TOWER		EVAPCO, INC. Evapeo		DWG. # CT4C071224-DRA-S	REV
MODEL #	AT 17-2H12	SCALE NTS	EVAPCO, II	NC. Evaluation	SERIAL #	DATE _{11/12/2025}
2. HÉAVIES 3. MPT DE FPT DEN BFW DE GVD DE FLG DEN 4. +UNIT W ACCESS 5. 3/4" [19N REFER T SUPPOF 6. DIMENS ENGL [MET 7. MAKE-U	I MOTOR LOCATION ST SECTION IS FAN/CAS NOTES MALE PIPE THRE NOTES FEMALE PIPE TH NOTES BEVELED FOR W NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUSORIES (SEE ACCESSOR MM] DIA. MOUNTING HOLE TO RECOMMENDED STE RT DRAWING IONS LISTED AS FOLLOV LISH FT-IN RIC] [mm] P WATER PRESSURE IN [137 kPa], 50 psi MAX [EAD READ VELDING JDE RY DRAWINGS) ES. EL		FACE B PLAN VIEW	FACE C ACCESS DOOR FACE A	FACE D
	1'-9 3/8" [543] 8" [200] BFW/GVD INLET	3'-8"	1'-2" [356] -2" [50] MPT MAKE-UP 7'-7 3/8" [2319] -3" [80] MPT DRAIN 4 1/4" [107] 1'-11 1/8"	2'-11 3/8" [899] 4'-5 1/8" [1349] 2" [51] 4'-3 7/8" [1318]		
	_	3" [80] MPT — 0VERFLOW 8" [200] — BFW/GVD 0UTLET 3'-1 3 [959	5 1/4"	1 3/8"	11'-11 3/4"	

 SHIPPING WEIGHT
 4730 lbs+ [2150] kg+
 OPERATING WEIGHT
 8090 lbs+ [3670] kg+
 HEAVIEST SECTION WEIGHT
 3080 lbs+ [1400] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY: MBG