JNIT	COOLING TOWER		EVADOO TN	DWG. # T4284848-DRA-ST	REV	
MODEL #	AT 428-4Q48	SCALE NTS	EVAPCO, IN	C.	SERIAL #	DATE _{10/29/2025}
2. HÉAV 3. MPT I FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. 3/4" [1 RECC 7. DIMEI 8. PAN F EVAP BY O1 9. PAN E	AN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THRE/ IENOTES FEMALE PIPE THRE/ IENOTES BEVELED FOR WID DENOTES GROOVED IENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR) -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 9MM] DIA. MOUNTING HOLE MENDED STEEL SUPPORT NSIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC] MM FUME BOX EQUALIZERS SL CO. PAN EQUALIZER PIPING THERS. EQUALIZER NIPPLE IS 11'-10 EACH STEP SIDE.	AD READ READ ELDING DE Y DRAWINGS) 44 kPa] ES. REFER TO DRAWING. /S: UPPLIED BY G IS SUPPLIED	FACE PLAN VIEV		ACE C (4) ACCESS DOOR ACE A	FACE D
2" [51] -	(4) 14" [350] — BFW/GVD OUTLET	11'-6" [3505]	7" [178] 1'-5 1/4" [438] 11'-2 1/4" [3410] 19'-5 1/2" [5931] 13'-3 3/4" [4058]	11'-10 1/2" (4) 14" [350] BFW/GVD INLET 9 1/8" [232]	(4) 12" [300] BRW/GVD EQUALIZER	
SHIPPING WEIGHT	(4) 4" [100] MPT OVERFLOW (4) 3" [80] MPT MAKE-UP (4) 4" [100] MPT DRAIN 5 1/8" [130] 28'-3 5/ [8626 FACE I	B OPER	1'-5 3/8" [441] 9" [229] 4" [102]		(SEE NOTE #9) 3'-7" [1092] 51'-1" [5570]	1 1/2" [38] RAWN BY: MER