



UNIT COOLING TOWER		EVAPCO, INC. 	DWG. # T3090848-DRD-ST	REV. -
MODEL # AT 19-4J8	SCALE NTS		SERIAL #	DATE 9/10/2025

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B




FACE B

FACE A



FACE A

FACE C



FACE D

FACE B

PLAN VIEW

SHIPPING WEIGHT 4180 lbs+ [1900] kg+	OPERATING WEIGHT 6600 lbs+ [2995] kg+	HEAVIEST SECTION WEIGHT 2910 lbs+ [1320] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: JLG
---	--	---	-------------------------------	------------------