					Tana a	1
UNIT COOLING TOWER			EVADOO T	NC evapco	DWG. # CT4C071236-DRA-ST	REV.
MODEL #	AT 17-3K12	SCALE NTS	TEVAPCO, I	NC. Evapeo	SERIAL #	DATE 11/14/2025
2. HEAVIES 3. MPT DEN FPT DEN BFW DEI GVD DEN FLG DEN 4. +UNIT W ACCESS 5. 3/4" [19M REFER T SUPPOR 6. DIMENSI ENGL [METF 7. MAKE-Uf	MOTOR LOCATION IT SECTION IS FAN/CASIN IOTES MALE PIPE THREA IOTES FEMALE PIPE THREA IOTES FEMALE PIPE THREA IOTES GROOVED IOTES FLANGE EIGHT DOES NOT INCLUE IORIES (SEE ACCESSORY IM) DIA. MOUNTING HOLE O RECOMMENDED STEE T DRAWING ONS LISTED AS FOLLOW ISH FT-IN RIC] [mm] WATER PRESSURE IN [137 kPa], 50 psi MAX [34]	ND EAD ELDING DE DRAWINGS) S. L	1¹-2" [356]	FACE B PLAN VIEW	FACE C ACCESS DOOR FACE A	FACE D
	1'-9 3/8" [543] 8" [200] BFW/GVD INLET	3" [80] MPT — OVERFLOW 8" [200] BFW/GVD OUTLET	3'-8" [1118] -2" [50] MPT MAKE-UP -3" [80] MPT DRAIN -3" [80] MPT DRAIN -1'-11 1/8" [587] -1'-2 7/8" [378] -1'-9 1/4" [540] -1'-9 1/4" [190] -3 5/8" [91]	2'-11 3/8" [899] 12'-8 3/8" [1654] 2" [51] 4'-3 7/8" [1318] 1 3/8"		
T'-4"						
SHIPPING WEIGHT	5210 lbs+ [236	5] kg+	OPERATING 8570 lbs+ [3890] kg+	HEAVIEST SECTION 3560 lbs+	[1615] kg+ NO. OF SHIPPING SECTIONS 2	DRAWN BY: MBG