INIT	COOLING TOWER	
IODEL #	AT 314-4072	SCALE NTS



DWG. # REV. T4147248-DRA-ST DATE_{12/13/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT **DRAWING**


7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]

FACE B





FACE C



FACE D

FACE A

