UNIT				DWC #	DEV/
	COOLING TOWE		EVAPCO, INC. Evaped	T4143624-DRA-ST	REV _
MODEL #	AT 214-2M36	SCALE NTS	LVAPCO, INC.	SERIAL#	DATE: 11/21/2025
2. HEAVII 3. MPT D FPT DE BFW D GVD D FLG DE 4. +UNIT ACCES 5. 3/4" [18 REFER SUPPO 6. DIMEN [ME 7. MAKE-	AN MOTOR LOCATION IEST SECTION IS FAN/CA DENOTES MALE PIPE THE ENOTES FEMALE PIPE TO DENOTES BEVELED FOR DENOTES GROOVED ENOTES FLANGE 'WEIGHT DOES NOT INCO SSORIES (SEE ACCESSO 9MM] DIA. MOUNTING HO R TO RECOMMENDED ST ORT DRAWING ISIONS LISTED AS FOLLO GLISH FT-IN ETRIC] [mm] -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX	READ THREAD R WELDING CLUDE ORY DRAWINGS) DLES. TEEL OWS:	FACE B PLAN VIEW	FACE A	FACE D
		7" [179]	1'-5 1/4" [438] (M) ACCESS	(M) ACCES	
		9'-5 1/8" [2873] 2 1/8" [54] 17'-8 3/8" [53	9'-0"	DOOR L	(2) 14" [350] BFW/GVD INLET
		8'-3 1/4" [2521]			
-	13'-11 1/4" [4248]	3/8"	1'-5 3/8" [441] 9" [229] 3 5/8" [92] 17'-6 7/8" [5356] 18'-0" [5486]	2) 9 [69] FPT DRAIN 2 1/2" [64]	(2) 14" [350] BFW/GVD OUTLET
	FACE B		-	36'-2 1/2" [11036]	

HEAVIEST SECTION WEIGHT

10440 lbs+ [4740] kg+

SHIPPING WEIGHT

31020 lbs+ [14075] kg+

OPERATING WEIGHT

50440 lbs+ [22880] kg+

FACE A

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG