EVAPCO, INC. PMRC-1988 SCALE NTS
NOTES: 1. (M) FAN MOTOR LOCATION. 1. (M) FAN MOTOR LOCATION. 2. MFD DENVISES BEFALLE PIPE THREAD BRY DENVISES BEFALLED FOR WELDING GVI DENVISES BROUGH FLO ENVISES PLANKE ACCESSORIES (SEE ACCESSORY PRAWINGS) 4. 334* Tipsmil DilA. MOJUNTING HOUES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-LIP WATER PRESSURE 20 ps (137 Mps) MIN. 50 ps) (344 Mps) MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENCLISH FI-NI (METRIC (Imm) (METRIC (Imm) T APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
1. (M) - FAM MOTOR LOCATION. 2. MPT DEND'ES FEMALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BPW DENOTES SEVELED FOR WELDING GVD DENOTES GROOVED FLIG DENOTES FLANGE FPE DENOTES PLANE RIO 3. MUNT WORTH PIPE STEAMS FPE DENOTES PLANE RIO 4. 304 Tipomi DIA MOUNTING HOLES PEFER TO RECOMMENDES TEELS SUPPORT DENAWING. 5. MAKE-UP WATER PRESSURE 20 pai (137 kPa) MIN, 50 pai (344 kPa) MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENCLISH FI-RI [METRIC] [min] V APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
[937] [1743]
OVERSIZED ACCESS DOORS 3'-11 3/4" [1213] * 7'-2 5/8" [2200] 9'-11" [3023] * 8'-6 3/8" [2600] 1'-8" [508] 3'7/8" [98] 3'7/8" [98] 1'-8" [508] 1'-8" [508] 1'-8" [508] 1'-6 1/8" [508] 1'-6 1/8" [508]
[1534] 11'-10 3/8" [3616] FACE B SHIPPING 67220 lbs+ [30495] kg+ OPERATING WEIGUT 25140 lbs+ [11405] kg+ NO. OF SHIPPING SECTIONS 3 DRAWN BY: JLG