UNIT COOLING TOWER			EVAPCO, INC. evapco				DWG. #	DWG. # T4145260-DRA-ST	
10del #	AT 214-5O52	SCALE NTS	EVA	PCO, II	VC.	1	SERIAL #		DATE _{11/22/2025}
2. HÉAVIE 3. MPT DE FPT DE BFW DE GVD DE FLG DE PE DEN 4. +UNIT V 4. +UNIT V 20 psi M 6. 3/4" [19] REFER DRAWII 7. DIMENS	N MOTOR LOCATION ST SECTION IS UPPER SE ENOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES BEVELED FOR WIE ENOTES FLANGE IOTES FLAIN END WEIGHT DOES NOT INCLUI SORIES (SEE ACCESSORY JP WATER PRESSURE IMM] DIA. MOUNTING HOLE TO RECOMMENDED STEE NG SIONS LISTED AS FOLLOW SCLISH FT-IN TRIC] [mm]	AD EAD ELDING DE / DRAWINGS) 44 kPa] ES. EL SUPPORT	FACE B PLAN VIEW		(2) ACCESS DOOR	FACE C		(2) ACCESS DOOR	FACE D
		7" [178]	1'-3 1/4" [387]						
		12'-1/4" - 2" [3664] - [51]	1/2"	12'-10 1/2" [3923]				(2) 14" [350] BFW/GVD INLET	
		10'-3 1/4" [3131]	16'-3 3/4" [4972] 2'-2" [660]				(2) 3" [80)) MPT —(2) 14" [350]	
-	13'-11 1/4"	_ 3/8 " _ [9]	1'-5 3/8" [441] 9" [229] 4 1/8"	19'-2 5/ [5858	25'-0" [7620] 25'-9" [7849]		MAKE-UP (2) 4" [100] FPT OVERFLOW (2) 4" [100] FPT DRAIN 2 1/2" [64]	BFW/GVD OUTLET	
	FACE B	r > 1				FACE A			
SHIPPING	49840 lbs+ [226	1.	PERATING 92500 L	bs+ [37875] kg+	HEAVIEST SECTION	18160 lbs+ [8240] k	I NO OF C	HIPPING SECTIONS 4	DRAWN BY: