UNIT **COOLING TOWER** SCALE NTS MODEL # AT 217-3I12


EVAPCO, INC. Evapeo





DWG. # REV. T3171236-DRG-ST DATE<sub>11/22/2025</sub> SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]







DRAWN BY: KDS NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 11340 lbs+ [5145] kg+ 19060 lbs+ [8650] kg+ 3820 lbs+ [1735] kg+ WEIGHT WEIGHT WEIGHT