UNIT	COOLING TOWER	
MODEL #	AT 224-4N18	SCALE NTS


EVAPCO, INC. Evapco


DWG. # T3241848-DRF-ST REV. SERIAL # DATE\_11/21/2025


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES.
  REFER TO RECOMMENDED STEEL SUPPORT
  DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]

## **FACE C**







 
 SHIPPING WEIGHT
 26160 lbs+ [11870] kg+
 OPERATING WEIGHT
 44700 lbs+ [20280] kg+
 HEAVIEST SECTION WEIGHT
 8700 lbs+ [3950] kg+
 NO. OF SHIPPING SECTIONS WEIGHT
 4
 DRAWN BY: KDS