NIT	CONDENSER		
IODEL#	PMRC-488	SCALE	NTS


EVAPCO, INC. Evapco

CEWR121208-DRA-ST SERIAL# 11/27/2025


NOTES:


- 1. (M)- FAN MOTOR LOCATION.
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.





FACE A





FACE A

DRAWN BY:

SHIPPING 18110 lbs+ [8215] kg+ WEIGHT

OPERATING WEIGHT

FACE B

22900 lbs+ [10390] kg+

HEAVIEST SECTION WEIGHT

12360 lbs+ [5610] kg+

NO. OF SHIPPING SECTIONS

JLG