JNIT	CONDENSER		
MODEL #	PMRC-408	SCALE	NTS


EVAPCO, INC. Evapco


CEWR121208-DRA-ST SERIAL# 11/27/2025


## NOTES:

- 1. (M)- FAN MOTOR LOCATION.
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 7. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.









**FACE A** 

NO. OF SHIPPING SECTIONS

DRAWN BY: **JLG** 

SHIPPING 17940 lbs+ [8140] kg+ WEIGHT

OPERATING WEIGHT

**FACE B** 

22730 lbs+ [10315] kg+

HEAVIEST SECTION WEIGHT

12360 lbs+ [5610] kg+