NUT						- va	 DW0 #	I pry
NIT	CONDENSER	•	FV/	<b>APCO</b>	TNC	evapco	CEWRTM1210-DRA-ST	REV -
IODEL#	PMRC-457	SCALE NTS		AI 00	<i>,</i> 11101		SERIAL#	DATE: 11/27/2025
FPT DENOTES BFW DENOTES GVD DENOTES PE DENOTES PE DENOTES 3. +UNIT WEIGHT ACCESSORIES 4. 3/4" [19mm] DI/ RECOMMENDI 5. MAKE-UP WAT 50 psi [344 kPa 6. DIMENSIONS L ENGLISH FT-I [METRIC] [mm 7. * - APPROXIMA*	S MALE PIPE THREAD S FEMALE PIPE THREAD S FEMALE PIPE THREAD S BEVELED FOR WELDING S GROOVED S FLANGE PLAIN END IT DOES NOT INCLUDE S (SEE ACCESSORY DRAWIN IA. MOUNTING HOLES. REFEF DED STEEL SUPPORT DRAWIN TER PRESSURE 20 psi [137 kF a] MAX. LISTED AS FOLLOWS: -IN	R TO ING. Pa] MIN,				FACE B PLAN VIEW	FACE C	FACE D
	2'-6 3/8" * [772]	4'-9" * [1448]	-					
			O	[997] *		6'-6 1/8" [1984]		
2"[50] MP' MAKE UI	OVERSIZED ACCESS DOORS	· [100] PE .	REFRIG OUT 9'-11" [	15'-0 1/2" [4585 <u>]</u> 3023] *	1	8'-6 3/8" [2600]		
3"[80] D 2'-5"[737] 1'-8" [508] 3	ÖRAIN	3"[8 OVE	D] MPT RFLOW			1'-7 1/8" [486]-	11'-11 3/4" [3651]	
	[130] 4 3/4" [121] 3'-10 1/2" [1181]	9'-9 3/4" [2991] <b>FACE B</b>					FACE A	

HEAVIEST SECTION WEIGHT

12420 lbs+ [5635] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG

SHIPPING WEIGHT

17750 lbs+ [8055] kg+

OPERATING WEIGHT

21620 lbs+ [9810] kg+