NIT	CONDENSES					DWG.#	REV
ODEL#	CONDENSER	SCALE N.T.O.	EVAPC	O. TNC.	evapco	CEWRTM1214-DRA-ST	- DATE:
ODEL#	PMRC-491	NTS		0, 1		SENIAL #	11/27/2025
2. MPT DENOT FPT DENOTI FPT DENOTI BFW DENOT GVD DENOT FLG DENOT ACCESSORI 4. 3/4" [19mm] I RECOMMED 50 psi [344 kl 6. DIMENSION ENGLISH F [METRIC] [7. * - APPROVI	S PLAIN END SHT DOES NOT INCLUDE IES (SEE ACCESSORY DRAWIN DIA. MOUNTING HOLES. REFEI IDED STEEL SUPPORT DRAWIN IATER PRESSURE 20 psi [137 kl Pa] MAX. S LISTED AS FOLLOWS: T-IN	ER TO ING. (Pa] MIN,			FACE B PLAN VIEW	FACE C	FACE D
						FACE A	
	2'-6 3/8" * [772]	4'-9" * [1448]					
	(2) 4*	O	O		7'-2 5/8" [2200]		
	(2) 4"	" [100] PE	O				
2'-5"[737]	EUP (80) MPT DRAIN		9'-11" [3023] *	1]	8'-6 3/8" [2600]		
1'-8" [508] ^{_]} 3	7/8" [98] 5 1/8" [130] 4 3/4" [121] 3'-10 1/2" [1181]	9'-9 3/4" [2991]] MPT RFLOW		1'-7 1/8" [486]	11'-11 3/4" [3651]	
		FACE B				FACE A	

HEAVIEST SECTION WEIGHT

16720 lbs+ [7585] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG

OPERATING WEIGHT

26070 lbs+ [11830] kg+

SHIPPING WEIGHT

22050 lbs+ [10005] kg+