

UNIT	CONDENSER
MODEL #	PMRC-2138

**EVAPCO, INC.**




DWG. # CEWR124014-DRA-ST

REV -  
SERIAL # DATE: 1/15/2026


**NOTES:**

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING.


**FACE C**



**FACE B**  
**PLAN VIEW**



**FACE B**



**FACE A**

SHIPPING  
WEIGHT

84150 lbs+ [38170] kg+

OPERATING  
WEIGHT

101200 lbs+ [45905] kg+

HEAVIEST SECTION  
WEIGHT

33040 lbs+ [14990] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**