

UNIT	CONDENSER	
MODEL #	eco-PMRC-1052	SCALE NTS

# EVAPCO, INC.



DWG. # CEWRTM3604-DRA-ST

REV

SERIAL #

DATE:

2/19/2026


**NOTES:**

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING



## FACE C

## **FACE B**

## PLAN VIEW



## **FACE A**



**SHIPPING  
WEIGHT**

37380 lbs+ [16960] kg+

## OPERATING WEIGHT

48970 lbs+ [22215] kg+

## HEAVIEST SECTION WEIGHT

14180 lbs+ [6435] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY

JLG