UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 17-6K14-Z


EVAPCO, INC. evapco





DWG. # REV. EG171412-DRC-SF DATE<sub>11/17/2025</sub> SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [18mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 10. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







**SHIPPING** WEIGHT

42740 lbs+ [19390] kg+

**OPERATING** WEIGHT

59280 lbs+ [26890] kg+

HEAVIEST SECTION WEIGHT

19290 lbs+ [8750] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: \*\*Drawn\*\*