


UNIT		CONDENSER		<div>EVAPCO, INC.</div> <div></div>	DWG. #	EG091412-DRC-ST	REV.	-
MODEL #		eco-ATC-438A	SCALE		NTS	SERIAL #		DATE

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE

ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE

FOR PRE-FABRICATION OF CONNECTING

PIPING

7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO

RECOMMENDED STEEL SUPPORT DRAWING.


8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]


FACE B

PLAN VIEW



FACE A

FACE A



SHIPPING WEIGHT	21300 lbs+ [9665] kg+	OPERATING WEIGHT	26440 lbs+ [11995] kg+	HEAVIEST SECTION WEIGHT	19220 lbs+ [8720] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY:	JLG
-----------------	-----------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----