

UNIT	CONDENSER
MODEL #	eco-PMRC-559

**EVAPCO, INC.**



DWG. # CEWRTM1212-DRA-ST

REV -


SERIAL #

DATE: 2/20/2026

**NOTES:**

- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING.



FACE C



FACE B

PLAN VIEW

FACE D



FACE B

FACE A

SHIPPING  
WEIGHT

24490 lbs+ [11110] kg+

OPERATING  
WEIGHT

28430 lbs+ [12900] kg+

HEAVIEST SECTION  
WEIGHT

18900 lbs+ [8575] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG