UNIT **CONDENSER** MODEL # SCALE NTS eco-ATC-332A

EVAPCO, INC. Evapeo




DWG. # REV. EG091208-DRC-ST DATE_{10/29/2025} SERIAL #


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





FACE A





SHIPPING OPERATING 14080 lbs+ [6390] kg+ 18250 lbs+ [8280] kg+ WEIGHT WEIGHT

HEAVIEST SECTION WEIGHT

12210 lbs+ [5540] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG