

UNIT	CONDENSER
MODEL #	ATC-1026E

EVAPCO, INC.




DWG. # C4122410-DRA-ST

REV -
SERIAL #
DATE: 2/4/2026

NOTES

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
5. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



SHIPPING
WEIGHT

38540 lbs+ [17485] kg+

OPERATING
WEIGHT

51580 lbs+ [23400] kg+

HEAVIEST SECTION
WEIGHT

31920 lbs+ [14480] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG