

UNIT	CONDENSER
MODEL #	eco-PMRC-1067

EVAPCO, INC.



DWG. # CEWR122010-DRA-ST

REV -


SERIAL #

DATE: 2/19/2026

NOTES:

- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE C




FACE D

FACE B

PLAN VIEW



FACE B



FACE A

SHIPPING
WEIGHT

41470 lbs+ [18815] kg+

OPERATING
WEIGHT

49540 lbs+ [22475] kg+

HEAVIEST SECTION
WEIGHT

31900 lbs+ [14470] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG