UNIT	COOLING TOWER		
MODEL#	AT 114-2K18	SCALE NTS	

## EVAPCO, INC. Evapco



**FACE B** 


**PLAN VIEW** 

T4141824-DRA-ST SERIAL# 11/10/2025

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]






**FACE D** 

**FACE A** 





**FACE B** 

**FACE A** 

SHIPPING 15600 lbs+ [7080] kg+ WEIGHT

OPERATING WEIGHT

25310 lbs+ [11485] kg+

HEAVIEST SECTION WEIGHT

10370 lbs+ [4705] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

**JLG**