UNIT CONDENSER		EVAPCO, INC. Evapco			WG. # WB3122008-DR	C-ST REV	
MODEL #	ATC-791E	SCALE NTS	EVAPCO,	TINC.	SE	ERIAL #	DATE 11/4/2025
2. HEAVIE 3. MPT DI FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT 4. +UNIT 20 psi N 6. *-APPE FOR PI PIPING 7. 3/4" [18 RECOM	IN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU ISORIES (SEE ACCESSOR UP WATER PRESSURE WIM [137 kPa], 50 psi MAX [ IOXIMATE DIMENSIONS D RE-FABRICATION OF CON INTERPRESE SUPPOR IMMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	EAD READ READ VELDING  JDE RY DRAWINGS)  344 kPa] O NOT USE NECTING  RES. REFER TO RT DRAWING.	PLA	FACE B	FACE	ACCESS DOOR	FACE D
			7" [ 178] ¬		<u>FACE</u>	<u>A</u>	
			[ 178]	1'-3 1/4" [ 387 ]			
	<u> </u>	_ <u> </u>	3'-3/8"			<u> </u>	
		5'-9 1/4" *	3'-3/8" *			M	
	2'-6 3/4" * (2) 4" [100	O	15'-2 3/8"				
	2" [50] MPT — MAKE-UP 2'-1 1/4" [643]		6" * 6'-2 1/4" [ 1884]				
	3 5/8" 3" [8 DRAI	0] MPT 3" [80] OVERFL 1/4" 33]	MPT				
	41						
	-	11'-10"		2'-1/2" [ 622 ]	20'-0"	1	
		FACE B		[ <b>022</b> ]	FACE A	-	
SHIPPING WEIGHT	26350 lbs+ [11	955] kg+ OPE	RATING 37840 lbs+ [17165] kg+	HEAVIEST SECTION	N 21840 lbs+ [9910] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: SLR