JNIT	CONDENSER		EVADOO	TNC evapeo	DWG. # WB3243608-DRC-ST	REV.
MODEL #	ATC-2647E	SCALE NTS	EVAPCO,	INC. evapco	SERIAL #	DATE 10/30/2025
2. HEAVIE: 3. MPT DE FPT DEI BFW DE GVD DE FLG DEI PE DEN: 4. +UNIT W +CCESS 5. MAKE-U 20 psi M 6. *-APPRC FOR PR PIPING 7. 3/4" [19n RECOMI	MOTOR LOCATION ST SECTION IS UPPER SI NOTES MALE PIPE THRE NOTES FEMALE PIPE THRE NOTES BEVELED FOR W NOTES GROOVED NOTES FLANGE OTES PLAIN END VEIGHT DOES NOT INCLU GORIES (SEE ACCESSOR IP WATER PRESSURE IN [137 kPa], 50 psi MAX [5 DXIMATE DIMENSIONS DC E-FABRICATION OF CONI nm] DIA. MOUNTING HOL MENDED STEEL SUPPOR SIONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ READ FELDING JDE Y DRAWINGS) 344 kPa] O NOT USE NECTING ES. REFER TO RT DRAWING.	PLAN	FACE B VIEW	FACE A (4) ACCESS DOOR FACE A	FACE D
2'-1 1/4' [643] 1'-5 [433	(4) 2" [50] MAKI (4) 3" [80] D	MPT - 11'-4	9'-1/8" [2748] **EFRIG IN **EFRIG OU ** [5242] 6" ** [154] * * [2494] 4'-8" [1422] 43/4" 6394" 699]	1'-3 1/4" [387]	1'-11 1/8" — 36'-2 1/2" [11036]	

FACE B

FACE A