NIT CONDENSER	EVADO 1	NC evapco	DWG. # CEWR123610-DRA-ST	REV -
PMRC-1296 SCALE NT	EVAPCO, I	NC. evapco	SERIAL#	DATE: 11/25/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE B PLAN VIEW	FACE C		FACE D
3'-0 7/8" * 5'-8 5/8" * [1743]		FACE A		
OVERSIZED O O REFRIG IN O REFRIG OU 3"[80] MPT [130]	3'-3 1/4" [997] * 6'-6 1/8" [1984] 15'-0 1/2" [4585] 9'-11" [3023] * 8'-6 3/8" [2600]			1'-6 1/4" [464]
3 7/8 [96] OVERFLOW [1534] 11'-10 3/8" [3616] FACE B SHIPPING WEIGHT 58490 lbs+ [26535] kg+	OPERATING	FACE HEAVIEST SECTION WEIGHT 21790 lbs+ [9885] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG