UNIT	CONDENSER	
MODEL #	ATC-2855E	SCALE NTS

EVAPCO, INC. EVAPCO

DWG. # WB3244008-DRC-ST REV. SERIAL # DATE<sub>10/30/2025</sub>

DRAWN BY:

## NOTES:

**SHIPPING** 

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]




**PLAN VIEW** 

HEAVIEST SECTION

WEIGHT



**FACE C** 




**FACE B** 

104860 lbs+ [47565] kg+

**OPERATING** 

WEIGHT

151000 lbs+ [68495] kg+



21680 lbs+ [9835] kg+

NO. OF SHIPPING SECTIONS