CONDENSER	EVADOO 1	CNC evapco	CEWR123608-DRA-ST	REV -
ODEL# PMRC-1376 SCALE N	EVAPCO, I	INC. evapeo	SERIAL#	DATE: 11/27/2025
NOTES:  1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE B PLAN VIEW	FACE C		FACE D
3'-0 7/8" * 5'-8 5/8" * [937]		FACE A		
OVERSIZED ACCESS DOORS  3"[80] MPT MAKE UP  3"[80] MPT DRAIN  2'-5"[737]  1'-8" [508]  3 7/8" [98]  11-10 3/8"  [3616]	2-6 3/4" [/81] * 3-9 3/8 [1/00]  14'-4" [4369]  9'-11" [3023] * 8'-6 3/8" [2600]			1'-6 1/4" [464]
FACE B		FACE A		
SHIPPING WEIGHT 51710 lbs+ [23460] kg+	OPERATING WEIGHT 66330 lbs+ [30090] kg+	HEAVIEST SECTION 18210 lbs+ [8260] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG